Fresh Technology



Fresh-Lock® Style 113 Extra-Wide, Easy-Grip Zipper

- Extra-wide offset flange provides an increased gripping area for easy consumer opening
- Excellent sealability to a wide variety of films maximizes seal integrity and minimizes leakage
- Lower sealing temperatures made possible with patented ribs promote faster line speeds and reduce film distortion to enhance package appearance
- Strong holding force keeps contents secure
- Suitable for horizontal form/fill/seal equipment or preformed pouches
- Single-zipper channel snaps securely closed to keep contents fresh

Get a Grip on Zipper Performance

One of the widest FRESH-LOCK® zipper styles available, the 113 features patented sealant ribs ensure a strong bond between zipper and film, plus plenty of gripping room for consumers. Easy open and reclose features make the 113 a great choice for a variety of products, including hard-to-hold items like dried fruits and nuts that require a tight seal to maintain freshness.

Zipper Specification

Product Description: STYLE 113 - Sealant Layer

GKL07425-1 Medium Reusable Spool
GKL07426-1 Large Reusable Spool
GKL07525-1 Medium Recyclable Spool
GKL07526-1 Large Recyclable Spool

PROFILE WEIGHT: WIDTH MEASUREMENTS: FOOTAGE/SPOOL:

2.6 grams/ft +/- 0.1 grams/ft 19.2 mm +/- 1.0 mm Medium Spool: 8,000 ft + 100 - 0 ft

Large Spool: 12,000 ft + 100 - 0 ft

SPOOLS/PALLET: FOOTAGE/PALLET: FINISHED SPOOL UNIT WEIGHT:

Medium Spool: 12 spools 96,000 ft + 1000 - 0 ft \sim 51 lbs Large Spool: 10 spools 120,000 ft + 1000 - 0 ft \sim 76 lbs

PACKAGING:

Medium Spool 15.49" width 1.5" shaft O.D. 19.75" flange O.D. Large Spool 15.81" width 1.5" shaft O.D. 23.50" flange O.D.

PROPERTIES:

Zipper material(s): LDPE blend with adhesive sealant

Suitable for food contact applications Sealing temperature range: **220-300 °F

Holding force from product side: 4.0 lbs target avg.

POSITION OF ZIPPER:

The post next to interlocking members must be positioned toward the product/inside of package.

Each spool individually wrapped & placed in individual shipping case.

Call your Fresh-Lock® zipper representative for details on our Zipper Spool Reuse Program.

www.Fresh-Lock.com







^{**}Temperature range may vary depending on type of package film used.